

PDV-65 Optima Arrester (15.3 kV MCOV, 7233 Hardware)

By OHIO BRASS
Catalog # 2132657233

IEEE Normal Duty Class / IEC Distribution Medium Polymer Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	Transformer Bracket
Cantilever Bending Strength - Max.	45 Nm
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution

Dimensions

Height	8.5 in
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	25.5 in (648 mm)
Current - Low Current Long Duration (LCLD) Test	75 A
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	59.7 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 47.2 kV @ 1.5 kA • 50.3 kV @ 3 kA • 53.6 kV @ 5 kA • 60.3 kV @ 10 kA • 69.7 kV @ 20 kA • 87.1 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	42.2 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	15
Time - Low Current Long Duration (LCLD) Test	2000 μ s

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters \(EU1587\)](#)
[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E_Catalog 70\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese \(17-5122C\)](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions \(17-5122\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French \(17-5122F\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish \(17-5122S\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Literature - Lightning Surge Arresters \(SF01023E\)](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits \(SF14069E\)](#)
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
OB-2132657233-SPEC-EN | REV 1/2024