

HUBBELL Power Systems

PVR Optima (29 kV MCOV, 7324 Hardware)

By OHIO BRASS
Catalog # [2216297324](#)

IEEE Riser Pole Class Polymer Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Application	Distribution
Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	135 Nm
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359418924

Dimensions

Height	21.1 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	14.0 in (355.6 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	16.0 in (406.4 mm)
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	52 in (1321 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	
Duty Cycle	36 kV
Frequency Rating	48-62 Hz
MCOV	29 kV
Maximum .5 Microsecond	107.2 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	82.2 kV @ 1.5 kA
	85.6 kV @ 3 kA
	89.2 kV @ 5 kA
	96.1 kV @ 10 kA
	106.2 kV @ 20 kA
	123 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	70.7 kV
Minimum Strike	18 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	
Withstand Voltage - 60 Hz Wet	76.4
Withstand Voltage - Lightning Impulse	180.3

Logistics

Pallet Quantity	35
-----------------	----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)

[Catalogs - Arresters IEEE & IEC Distribution Class](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Spanish](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Chinese](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - French](#)

[Installation Manuals - PDV-PVR Polymer Distribution Class](#)

[Arrester Installation Instructions](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.](#)

[Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)

[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)

[Literature - Lightning Surge Arresters](#)

[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)

[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-2216297324-SPEC-EN | REV 6/2024