

HUBBELL Power Systems

PVI-LP Arrester (12.7 kV MCOV / Uc)

By OHIO BRASS
Catalog # [214513CCAA](#)

IEC Class Station Medium Polymer Housed Surge Arrester



*Representative Image

Features

- PVI-LP arresters comply with the latest revision of IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

General

Application	Distribution
Bracket Type	None
Color	Gray Housing
Material	ESP™ Polymer Housing
Type	Station Low

Dimensions

Stud Type	M12
-----------	-----

Electrical Ratings

Duty Cycle	15 kV
Frequency Rating	48-62 Hz
MCOV	12.7 kV
Pressure Relief Capability-Symmetrical rms (kA)	40
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand