

PDV-65 Optima Arrester (5.1 kV Uc, CCBI Hardware)

By OHIO BRASS
Catalog # 294005CCBI

IEEE Normal Duty Class / IEC Distribution Medium Polymer
Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	NEMA Crossarm Bracket
Color	Gray
Material	ESP™ Polymer Housing
Type	Distribution

Dimensions

Stud Type	M12
-----------	-----

Electrical Ratings

Creep and Leakage Distance	15.4 in (391 mm)
Current - Low Current Long Duration (LCLD) Test	75A
Duty Cycle	6 kV
Frequency Rating	48-62 Hz
MCOV	5.1 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	20.7 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 16.3 kV @ 1.5 kA • 17.3 kV @ 3 kA • 18.5 kV @ 5 kA • 20.8 kV @ 10 kA • 24 kV @ 20 kA • 30 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	14.6 kV
Pressure Relief Capability-Symmetrical rms (kA)	15
Time - Low Current Long Duration (LCLD) Test	2000 microsec
Withstand Voltage - 60 Hz Wet	19.8
Withstand Voltage - Lightning Impulse	40.5

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters \(EU1587\)](#)
[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E_Catalog 70\)](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions \(17-5122\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese \(17-5122C\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French \(17-5122F\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish \(17-5122S\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Literature - Lightning Surge Arresters \(SF01023E\)](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)

(SF14069E)

Video - Hubbell Power Systems In Depth: Distribution Arresters (VI01037E0119)

Video - Hubbell Power Systems Metal Oxide Varistor (VI01022E0718)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
OB-294005CCBI-SPEC-EN | REV 1/2024