

PVI-LP Arrester (24.4 kV MCOV /  
Uc)

By OHIO BRASS  
Catalog # [214524C2CC](#)

IEC Class Station Medium Polymer Housed Surge Arrester



\*Representative Image

Features

- PVI-LP arresters comply with the latest revision of IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

Application

Distribution

General

Bracket Type	None
Catalog Number	214524C2CC
Color	Gray Housing
Material	ESP™ Polymer Housing

Dimensions

Height	16.3 in
--------	---------

Electrical Ratings

Current - Low Current Long Duration (LCLD) Test	550 A
Duty Cycle	30 kV
Frequency Rating	48-62 Hz
MCOV	24.4 kV

Certifications And Compliance

Industry Standard(s)	IEEE/IEC
----------------------	----------

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)  
[Catalogs - Station Class Surge Arresters IEEE and IEC](#)  
[Installation Manuals - PVI-LP PVI Polymer Arrester Installation Instructions](#)  
[Sales Drawings - 214524C2CC](#)  
[Specifications - Specification for Solid Core IEC Station Class Arresters](#)  
[Specifications - 214524C2CC](#)