

**PDV-65 Optima Arrester (29 kV
MCOV, 7314 Hardware)**

By OHIO BRASS
Catalog # [2175797314](#)

IEEE Normal Duty Class / IEC Distribution Medium Polymer
Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	None
Cantilever Bending Strength - Max.	45 Nm
Catalog Number	2175797314
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359524588

Dimensions

Height	20.8 in
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	46.2 in (1173 mm)
Current - Low Current Long Duration (LCLD) Test	75 A
Duty Cycle	36 kV
Frequency Rating	48-62 Hz
MCOV	29 kV
Maximum .5 Microsecond Discharge Volts @ Classifying	119.3 kV

Current

Maximum Discharge Voltage	<ul style="list-style-type: none">• 94.4 kV @ 1.5 kA• 100.5 kV @ 3 kA• 107.2 kV @ 5 kA• 120.7 kV @ 10 kA• 139.4 kV @ 20 kA• 202 kV @ 40 kA
---------------------------	---

Maximum Switching Surge Protective Level @ 500A	84.5 kV
Pressure Relief Capability-Symmetrical rms (kA)	15
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Certifications And Compliance

Industry Standard(s)	IEC
----------------------	-----

Logistics

Pallet Quantity	64
-----------------	----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Lightning Surge Arresters](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Specifications - Specification for IEEE Normal Duty Class Distribution Arresters](#)
[Specifications - 2175797314](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)
[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
OB-2175797314-SPEC-EN | REV 1/2025