

# HUBBELL Power Systems

## PVI-LP Arrester (19.5 kV MCOV / Uc)

By OHIO BRASS  
Catalog # [2184207214](#)

IEC Class Station Medium Polymer Housed Surge Arrester



\*Representative Image

### Features

- PVI-LP arresters comply with the latest revision of IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

### General

Application	Distribution
Bracket Type	None
Color	Gray Housing
Material	ESP™ Polymer Housing
Type	Station Low

### Dimensions

Stud Type	3/8-16
-----------	--------

### Electrical Ratings

Current - Low Current Long Duration (LCLD) Test	550
Duty Cycle	24 kV
Frequency Rating	48-62 Hz
MCOV	19.5 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	68.3 kV
Maximum Discharge Voltage	54.2 kV @ 1.5 kA 57.2 kV @ 3 kA 59.9 kV @ 5 kA 64.6 kV @ 10 kA 71.5 kV @ 20 kA 80.6 kV @ 40 kA
Pressure Relief Capability - Symmetrical rms (kA)	40
Time - Low Current Long Duration (LCLD) Test	2000 Qs
Withstand Voltage - 60 Hz Wet	53.6
Withstand Voltage - Lightning Impulse	84

### Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)  
[Catalogs - Arresters IEEE & IEC Distribution Class](#)  
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)  
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)  
[Video - Hubbell Power Systems In Depth: Distribution Arresters](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
OB-2184207214-SPEC-EN | REV 6/2024