

HUBBELL Power Systems

PVI-LP Arrester (29 kV MCOV / U_c)

By OHIO BRASS
Catalog # [3006293012](#)

IEEE Intermediate Class Polymer Housed Surge Arrester



*Representative Image

Features

- PVI-LP solid core station arresters comply with the latest revision of IEEE C62.11 and IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

General

Color	Gray Housing
Material	ESP™ Polymer Housing
Type	Intermediate
UPC	096359672302

Electrical Ratings

Frequency Rating	48-62 Hz
MCOV	29 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	111.3 kV
Maximum Discharge Voltage	84.4 kV @ 1.5 kA
	88.6 kV @ 3 kA
	92.8 kV @ 5 kA
	96.9 kV @ 10 kA
	108.8 kV @ 20 kA
Maximum Switching Surge Protective Level @ 500A	78.4 kV
Pressure Relief Capability-Symmetrical rms (kA)	40
Time - Low Current Long Duration (LCLD) Test	2000

Certifications And Compliance

Industry Standard(s) IEEE

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-3006293012-SPEC-EN | REV 6/2024