

HUBBELL Power Systems

PVI-LP Arrester (17 kV MCOV / Uc)

By OHIO BRASS
Catalog # 3008173001

IEEE Intermediate Class Polymer Housed Surge Arrester



*Representative Image

Features

- PVI-LP solid core station arresters comply with the latest revision of IEEE C62.11 and IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

General

Cantilever Bending Strength - Max.	4,000 in lbs
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Hardware	Single Eyebolt Terminals
Mounting Position	Small Top/Tripod Base
Type	Intermediate
UPC	096359263272

Dimensions

Bolt Circle Diameter	8.75 in
Diameter - Lug Hole	.56 in (14.224 mm)
Diameter - Single Bolt Hole(s)	0.5 in
Dimensions	10.313 in x 10.313 in x 13.750 in
Height	13.75 in
Length	10.313 in
Maximum Operating Altitude	12000 ft
Minimum Mounting Spacing on Center (Sea Level) - Phase to	6.2 in (157.48 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to	7.6 in (193.04 mm)
Phase	
Thickness - Lug	1.25 in (31.75 mm)
Weight	10 lb
Width	10.313 in

Electrical Ratings

Creep and Leakage Distance	30.8 in (782 mm)
Current - Low Current Long	550
Duration (LCLD) Test	
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond	62.4 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	46.9 kV @ 1.5 kA
	49.2 kV @ 3 kA
	51.5 kV @ 5 kA
	53.8 kV @ 10 kA
	60.4 kV @ 20 kA
	67.1 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	43.5 kV
Pressure Relief Capability-Symmetrical rms (kA)	40
Time - Low Current Long	2000
Duration (LCLD) Test	
Withstand Voltage - 60 Hz Wet	44.7
Withstand Voltage - Lightning Impulse	69.9

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Logistics

Pallet Quantity

18

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.
Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)

[Literature - Application Guide: Metal-oxide Surge Arresters for
use on AC systems](#)

[Sales Drawings - 3008173001 \(Reference Only\)](#)

[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-3008173001-SPEC-EN | REV 6/2024