

PVR Optima (10.2 kV MCOV, 7224 Hardware)

By OHIO BRASS
Catalog # 2216107224

IEEE Riser Pole Class Polymer Housed Surge Arrester

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	135 Nm
Catalog Number	2216107224
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359417972

Dimensions

Height	9.4 in
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	26 in (660 mm)
----------------------------	----------------



*Representative Image

Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	12 kV
Frequency Rating	48-62 Hz
MCOV	10.2 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	36.2 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 27.8 kV @ 1.5 kA• 29 kV @ 3 kA• 30.2 kV @ 5 kA• 32.5 kV @ 10 kA• 35.9 kV @ 20 kA• 41.6 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	23.9 kV
Minimum Strike	6.1 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Logistics

Pallet Quantity	192
-----------------	-----

Product Assets

[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Specifications - 2216107224](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)