

## PVI-LP Arrester (17 kV MCOV / Uc)

By OHIO BRASS  
Catalog # 3028173001

IEEE Intermediate Class Polymer Housed Surge Arrester



\*Representative Image

### Features

- PVI-LP solid core station arresters comply with the latest revision of IEEE C62.11 and IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

### General

Color	Gray
Material	ESP™ Polymer Housing
Mounting Hardware	Single Eyebolt Terminals
Type	Intermediate
UPC	096359672388

### Dimensions

Maximum Operating Altitude	12000 ft
----------------------------	----------

### Electrical Ratings

Current - Low Current Long Duration (LCLD) Test	550
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	56.9 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 45.1 kV @ 1.5 kA</li> <li>• 47.7 kV @ 3 kA</li> <li>• 49.9 kV @ 5 kA</li> <li>• 53.8 kV @ 10 kA</li> <li>• 59.6 kV @ 20 kA</li> <li>• 67.1 kV @ 40 kA</li> </ul>
Pressure Relief Capability- Symmetrical rms (kA)	40
Time - Low Current Long Duration (LCLD) Test	2000
Withstand Voltage - 60 Hz Wet	44.7
Withstand Voltage - Lightning Impulse	69.9

### Certifications and Compliance

Industry Standard(s)	IEEE
----------------------	------

### Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC \(CA01082E\\_Catalog 30\\_0923\\_web\)](#)  
[Installation Manuals - PVI-LP PVI Polymer Arrester Installation Instructions \(17-5150\)](#)  
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)

