

## PVR Optima (10.2 kV MCOV, 7333 Hardware)

By OHIO BRASS  
Catalog # 2216107333

IEEE Riser Pole Class Polymer Housed Surge Arrester



\*Representative Image

### Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

### Application

Distribution

### General

Bracket Type	Transformer Bracket
Cantilever Bending Strength - Max.	135 Nm
Color	Gray
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359671725

### Dimensions

Height	9.4 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to Ground	5.3 in (134.62 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	7.3 in (185.42 mm)
Stud Type	3/8-16

### Electrical Ratings

Creep and Leakage Distance	15.4 in (391 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	12 kV
Frequency Rating	48-62 Hz
MCOV	10.2 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	36.2 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> <li>• 27.8 kV @ 1.5 kA</li> <li>• 29 kV @ 3 kA</li> <li>• 30.2 kV @ 5 kA</li> <li>• 32.5 kV @ 10 kA</li> <li>• 35.9 kV @ 20 kA</li> <li>• 41.6 kV @ 40 kA</li> </ul>
Maximum Switching Surge Protective Level @ 500A	23.9 kV
Minimum Strike	6.1 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 $\mu$ s
Withstand Voltage - 60 Hz Wet	26.9
Withstand Voltage - Lightning Impulse	60.1

### Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters \(EU1587\)](#)  
[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E\\_Catalog 70\)](#)  
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions \(17-5122\)](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese \(17-5122C\)](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French \(17-5122F\)](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish \(17-5122S\)](#)  
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)  
[Literature - Lightning Surge Arresters \(SE01023E\)](#)



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
OB-2216107333-SPEC-EN | REV 1/2024