

# HUBBELL Power Systems

## Veri\*Lite VLS Insulator

By OHIO BRASS  
Catalog # [4050061400](#)

Suspension Clevis Tongue 69 kV.



### Features

- Made from tough, durable ESP polymer
- replaces six 10" x 5-3/4" distribution deadend bells

### General

Application	Suspension
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground/Base	Clevis
Fitting - Live Line End	Tongue
Material	ESP
Material - End Fitting	Steel
Material - Pin (Cotter)	Stainless Steel
Number of Sheds	12
Shed Style	Uniform
Strength Rating - Ultimate	15000 lb
Tensile Strength	15 kip
Tensile Strength - Routine	7500
UPC	096359264385

### Dimensions

Diameter - Shed(s)	5.9
Dimensions	36.06 in x 5.9 in x 5.9 in
Height	5.9 in
Length	36.06 in
Length - Effective	34.5 in
Rod Diameter	0.625
Thickness - Housing	0.15
Weight	7 lb
Width	5.9 in

### Electrical Ratings

Arc Distance - Dry	35.2
Creep and Leakage Distance	84 IN (2134 mm)
Critical Impulse Flashover (CIFO) - Negative	580
Critical Impulse Flashover (CIFO) - Positive	610
Flashover Voltage - 60 Hz Dry	370
Flashover Voltage - 60 Hz Wet	305
Voltage - Line	69000 V

### Certifications And Compliance

Industry Standard(s) ANSI

### Logistics

Pallet Quantity 96  
Standard Package 12

### Product Assets

[Catalogs - Veri\\*Lite Deadend & Suspension Insulators Catalog Literature - HUBBELL ESP™ INSULATORS NOT ALL POLYMER IS CREATED EQUAL](#)  
[Sales Drawings - Veri Lite Suspension Ins](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
OB-4050061400-SPEC-EN | REV 6/2024