

PVR Optima (19.5 kV MCOV, 7214 Hardware)

By OHIO BRASS
Catalog # 2216207214

IEEE Riser Pole Class Polymer Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	None
Cantilever Bending Strength - Max.	135 Nm
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359418559

Dimensions

Height	14.7 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to Ground	9.6 in (243.84 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	11.6 in (294.64 mm)
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	30.8 in (782 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	24 kV
Frequency Rating	48-62 Hz
MCOV	19.5 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	72.2 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 55.5 kV @ 1.5 kA • 57.8 kV @ 3 kA • 60.2 kV @ 5 kA • 64.9 kV @ 10 kA • 71.7 kV @ 20 kA • 83.1 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	47.8 kV
Minimum Strike	11.3 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 μs
Withstand Voltage - 60 Hz Wet	51.4
Withstand Voltage - Lightning Impulse	121.7

Logistics

Pallet Quantity	80
-----------------	----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters \(EU1587\)](#)
[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E_Catalog 70\)](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions \(17-5122\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese \(17-5122C\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French \(17-5122F\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish \(17-5122S\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)

ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.
Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems (TD01135E)
Literature - Lightning Surge Arresters (SF01023E)
Literature - Hubbell Arrester and Wildlife Guard Solution Kits (SF14069E)
Video - Hubbell Power Systems Metal Oxide Varistor (VI01022E0718)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
OB-2216207214-SPEC-EN | REV 1/2024