

PVR Optima (19.5 kV MCOV, 7533 Hardware)

By OHIO BRASS
Catalog # 2216207533

IEEE Riser Pole Class Polymer Housed Surge Arrester



Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	Transformer Bracket
Cantilever Bending Strength - Max.	135 Nm
Color	Gray
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution

Dimensions

Height	14.7 in
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	30.8 in (782 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	24 kV
Frequency Rating	48-62 Hz
MCOV	19.5 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	72.2 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 55.5 kV @ 1.5 kA• 57.8 kV @ 3 kA• 60.2 kV @ 5 kA• 64.9 kV @ 10 kA• 71.7 kV @ 20 kA• 83.1 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	47.8 kV
Minimum Strike	11.3 in
Pressure Relief Capability - Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 μs

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters \(EU1587\)](#)
[Catalogs - Arresters IEEE & IEC Distribution Class \(CA01065E_Catalog 70\)](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions \(17-5122\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese \(17-5122C\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French \(17-5122F\)](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish \(17-5122S\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Literature - Lightning Surge Arresters \(SF01023E\)](#)
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits \(SF14069E\)](#)
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
OB-2216207533-SPEC-EN | REV 1/2024