

## Protecta\*Lite Arrester (15.3 kV MCOV)

By OHIO BRASS  
Catalog # [602015B0F4011](#)

This web listing represents a sampling of typical configurations. Protecta\*Lite Arrester assemblies can be customized for all distribution and transmission lines.

Selection of arrester MCOV size is based upon the maximum continuous voltage that is applied across the arrester in service (line-to-ground). For arresters on effectively grounded neutral systems, this is normally the maximum line-to-ground voltage

*Example: 84 kV on a 138 kV system. For ungrounded or impedance-grounded systems, the MCOV should be at least 90 percent of maximum phase-to-phase voltage.*

For more information about arrester selection, please contact your Hubbell Power Systems representative.

### Features

- Eliminate lightning interruptions with Protecta\*Lite Arresters
- Custom designs available up to 765 kV
- Protecta\*Lite Arresters offer protection on both shielded and unshielded lines
- To learn more about how Protecta\*Lite improves line performance, click [here](#) to visit our blog.

### Application

35 kV and Below



### General

Catalog Number	602015B0F4011
Type	Line Arresters

### Product Assets

[Sales Drawings - 602015-B0-F4-011](#)

[Specifications - 602015B0F4011](#)

[Technical Publications - The Evolution of Line Surge Arrester Technology](#)



A Hubbell brand