

PVI-LP Arrester (5.1 kV MCOV / U_c)

By OHIO BRASS
Catalog # [3028053002](#)

IEEE Intermediate Class Polymer Housed Surge Arrester



*Representative Image

Features

- PVI-LP solid core station arresters comply with the latest revision of IEEE C62.11 and IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina

General

Color	Gray
Material	ESP™ Polymer Housing
Mounting Hardware	4-Hole NEMA Pad Line Terminal
Type	Intermediate

Dimensions

Maximum Operating Altitude	12000 ft
----------------------------	----------

Electrical Ratings

Current - Low Current Long Duration (LCLD) Test	550
Duty Cycle	6 kV
Frequency Rating	48-62 Hz
MCOV	5.1 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	17.1 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 13.6 kV @ 1.5 kA • 14.4 kV @ 3 kA • 15 kV @ 5 kA • 16.2 kV @ 10 kA • 17.9 kV @ 20 kA • 20.2 kV @ 40 kA
Pressure Relief Capability - Symmetrical rms (kA)	40
Time - Low Current Long Duration (LCLD) Test	2000
Withstand Voltage - 60 Hz Wet	13.5
Withstand Voltage - Lightning Impulse	21.1

Certifications and Compliance

Industry Standard(s)	IEEE
----------------------	------

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC \(CA01082E_Catalog 30_0923_web\)](#)
[Installation Manuals - PVI-LP PVI Polymer Arrester Installation Instructions \(17-5150\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
OB-3028053002-SPEC-EN | REV 1/2024