

HUBBELL Power Systems

Veri*Lite VLS Insulator

By OHIO BRASS
Catalog # [4050041400](#)

Suspension Clevis Tongue 46 kV.



Features

- Made from tough, durable ESP polymer
- replaces four 10" x 5-3/4" distribution deadend bells

General

Application	Suspension
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground/Base	Clevis
Fitting - Live Line End	Tongue
Material	ESP
Material - End Fitting	Steel
Material - Pin (Cotter)	Stainless Steel
Number of Sheds	8
Shed Style	Uniform
Strength Rating - Ultimate	15000 lb
Tensile Strength	15 kip
Tensile Strength - Routine	7500
UPC	096359264347

Dimensions

Diameter - Shed(s)	5.9
Length - Effective	23 in
Rod Diameter	0.625
Thickness - Housing	0.15
Weight	5 lb

Electrical Ratings

Arc Distance - Dry	23 in
Creep and Leakage Distance	54 IN (1372 mm)
Critical Impulse Flashover (CIFO) - Negative	435
Critical Impulse Flashover (CIFO) - Positive	420
Flashover Voltage - 60 Hz Dry	255
Flashover Voltage - 60 Hz Wet	190
Voltage - Line	46000/69000 V

Certifications And Compliance

Industry Standard(s)	ANSI
----------------------	------

Logistics

Pallet Quantity	48
Standard Package	12

Product Assets

[Catalogs - Veri*Lite Deadend & Suspension Insulators Catalog](#)
[Literature - HUBBELL ESP™ INSULATORS NOT ALL POLYMER IS CREATED EQUAL](#)
[Sales Drawings - Veri Lite Suspension Insulator](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-4050041400-SPEC-EN | REV 6/2024