

Veri*Lite VLS Insulator

By OHIO BRASS
Catalog # 4050051400

Suspension Clevis Tongue 69 kV.



*Representative Image

Features

- Made from tough, durable ESP polymer
- replaces five 10" x 5-3/4" distribution deadend bells

Application

Suspension

General

EU RoHS Indicator	Contact Manufacturer
Fitting - Ground/Base	Clevis
Fitting - Live Line End	Tongue
Material	ESP
Material - End Fitting	Steel
Material - Pin (Cotter)	Stainless Steel
Number of Sheds	10
Shed Style	Uniform
Strength Rating - Ultimate	15000 lb
Tensile Strength	15 kip
Tensile Strength - Routine	7500
UPC	096359264361

Dimensions

Diameter - Shed(s)	5.9
Dimensions	30.31 in x 5.9 in x 5.9 in
Height	5.9 in
Length	30.31 in
Length - Effective	28.75 in
Rod Diameter	0.625
Thickness - Housing	0.150
Weight	6 lb
Width	5.9 in

Electrical Ratings

Arc Distance - Dry	29 in
Creep and Leakage Distance	69 IN (1753 mm)
Critical Impulse Flashover (CIFO) - Negative	510
Critical Impulse Flashover (CIFO) - Positive	500
Flashover Voltage - 60 Hz Dry	315
Flashover Voltage - 60 Hz Wet	245
Voltage - Line	69000 V

Certifications and Compliance

Industry Standard(s)	ANSI
----------------------	------

Logistics

Pallet Quantity	48
Standard Package	12

Product Assets

[Catalogs - Veri*Lite Deadend & Suspension Insulators Catalog \(CA08051E\)](#)
[Literature - HUBBELL ESP™ INSULATORS NOT ALL POLYMER IS CREATED EQUAL \(AIK-INSUL-SF-EN-01387\)](#)
[Sales Drawings - Veri Lite Suspension Ins \(4050051400\) \(Reference Only\)](#)