

Protecta*Lite Arrester (88 kV MCOV)

By OHIO BRASS
Catalog # 682088G1G2003

This web listing represents a sampling of typical configurations. Protecta*Lite Arrester assemblies can be customized for all distribution and transmission lines.

Selection of arrester MCOV size is based upon the maximum continuous voltage that is applied across the arrester in service (line-to-ground). For arresters on effectively grounded neutral systems, this is normally the maximum line-to-ground voltage

Example: 84 kV on a 138 kV system. For ungrounded or impedance-grounded systems, the MCOV should be at least 90 percent of maximum phase-to-phase voltage.

For more information about arrester selection, please contact your Hubbell Power Systems representative.

Features

- Eliminate lightning interruptions with Protecta*Lite Arresters
- Custom designs available up to 765 kV
- Protecta*Lite Arresters offer protection on both shielded and unshielded lines
- To learn more about how Protecta*Lite improves line performance, click [here](#) to visit our blog.

Application

Above 35 kV

General

Catalog Number	682088G1G2003
Installation Type	Horizontal Post Assembly
Insulator Type	Quadri*Sil S250
Type	Line Arresters

Electrical Ratings

Creep and Leakage Distance	151.2 in (3840.5 mm)
Duty Cycle	108 kV
Frequency Rating	48-62 Hz
MCOV	88 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	354.4 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 265.5 kV @ 1.5 kA• 283.1 kV @ 3 kA• 300 kV @ 5 kA



*Representative Image

	<ul style="list-style-type: none">• 329.8 kV @ 10 kA• 371.3 kV @ 20 kA• 441.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	254.4 kV
Pressure Relief Capability-Symmetrical rms (kA)	20
Voltage - Line	138 kV

Certifications And Compliance

Industry Standard(s)	IEEE/IEC
----------------------	----------

Product Assets

- [Case Studies - Performance & Revenue Enhancements Utilizing Line Surge Arresters - White Paper](#)
- [Catalogs - Protecta*Lite Line Surge Arresters](#)
- [Installation Manuals - Installation Instructions Protecta*Lite Arresters - English](#)
- [Installation Manuals - Installation Instructions Protecta*Lite Arresters - Spanish](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Protecta*Lite](#)
- [Literature - Protecta*Lite Line Arrester Performance Study](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Specifications - 682088G1G2003](#)
- [Technical Publications - The Evolution of Line Surge Arrester Technology](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)
- [Video - Ohio Brass Protecta*Lite® Systems Surge Arresters](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-682088G1G2003-SPEC-EN | REV 10/2024