


Veri*Lite PDI DS-15 Deadend Insulator (Silicone)

By OHIO BRASS
Catalog # 8010150215

Silicone Polymer Clevis Tongue 15kV Deadend Insulator DS-28/PDI-15



*Representative Image

Features

- Weathersheds:
- These Veri*Lite Insulators are manufactured with silicone rubber with Ohio Brass proprietary compound, the same proven material used in Quadri*Sil Transmission Insulators.

Application

Deadend

General

Cantilever Bending Strength - Routine	7500
Construction Material - Main	Silicone Polymer
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground/Base	Clevis
Fitting - Live Line End	Tongue
Insulator Type	DS15
Material	Silicone Polymer
Material - End Fitting	Steel
Material - Pin (Cotter)	Stainless Steel
Number of Sheds	4
Shed Style	3.85" Major Diameter, 2.65" Minor Diameter
Strength Rating - Ultimate	15000 lb
Tensile Strength	15 K
Tensile Strength - Routine	7500
Type	PDI-15
UPC	096359433446

Dimensions

Diameter - Shed(s)	3.6
Length - Effective	12.5 in
Rod Diameter	0.625
Thickness - Housing	0.100
Weight	2.37 lb

Electrical Ratings

Arc Distance - Dry	8
Creep and Leakage Distance	16 IN (406 mm)
Critical Impulse Flashover (CIFO) - Negative	160
Critical Impulse Flashover (CIFO) - Positive	140
Flashover Voltage - 60 Hz Dry	110
Flashover Voltage - 60 Hz Wet	75
Voltage - Line	15000 V

Certifications and Compliance

Industry Standard(s)	ANSI DS-15
----------------------	------------

Logistics

Pallet Quantity	480
Standard Package	15

Product Assets

[Catalogs - Veri*Lite Deadend & Suspension Insulators Catalog \(CA08051E\)](#)
[Literature - Polymer Dead-End Insulators \(AIK-INSUL-SF-EN-01156C\)](#)
[Literature - AIK-INSUL-POLYMER-DEADENDS-SF-EN-2023](#)
[Sales Drawings - DS-15/PDI-15 DIST Dead End INS \(8010150215\) \(Reference Only\)](#)