

Veri*Lite Line Post Insulator SR 69
kV

By OHIO BRASS
Catalog # 80S0690010

Horizontal Line Post 69 kV Two Hole Blade / Stud Base 7/8"-9 Tap.

Features

- Weathersheds molded with proprietary silicone rubber
- Proven direct bond interface

Application


Horizontal Line Post

General

Cantilever Bending Strength - Max.	2470 Lbs (11.0 kN)
Cantilever Bending Strength - Routine	1235 Lbs. (5.5 kN)
Catalog Number	80S0690010
Fitting - Ground/Base	7/8" Stud Base
Fitting - Live Line End	Two Hole Blade
Material	Silicone
Material - End Fitting	Galvanized Steel
Number of Sheds	12
Tension Range	2500 lb
UPC	096359438762

Dimensions

Angle	0
Diameter - Shed(s)	7.5" (190mm) / 5.2" (132mm)



*Representative Image

Length - Effective	26.63 in
Rod Diameter	1.75 in
Thickness - Housing	0.15" (3.8mm)
Weight	16.9 lb

Electrical Ratings

Arc Distance - Dry	22.3" (566mm)
Creep and Leakage Distance	58.2" (1478mm)
Critical Impulse Flashover (CIFO) - Positive	360 kV
Flashover Voltage - 60 Hz Dry	230 kV
Flashover Voltage - 60 Hz Wet	180 kV
Voltage - Line	69000 V
Voltage Rating	69 kV
Withstand Voltage - Lightning Impulse (Positive)	330 kV

Certifications And Compliance

Industry Standard(s)	ANSI
----------------------	------

Product Assets

[Catalogs - Veri*Lite Line Post Insulators Catalog](#)
[Literature - Silicone Insulators](#)
[Sales Drawings - Veri Lite 69 KV Line Post \(Reference Only\)](#)
[Specifications - 80S0690010](#)