

HUBBELL Power Systems

EVP Arrester (12.7 kV MCOV / Uc)

By OHIO BRASS

Catalog # [EVP0013003001](#)

IEEE Station Class / IEC Station Medium Polymer Housed Surge
Arrester



Features

- EVP solid core station arresters comply with the latest revision of IEEE C62.11 and IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

General

Cantilever Bending Strength - Max.	20,000 lb.
Catalog Number	EVP0013003001
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Hardware	Single Eyebolt Terminals
Mounting Position	Upright
Type	Station
UPC	096359506256

Dimensions

Diameter - Bolt Circle Variable	8.75 to 10 in
Diameter - Lug Hole	.56 in (14.224 mm)
Diameter - Single Bolt Hole(s)	0.5 in
Dimensions	48.250 in x 10.313 in x 10.313 in
Height	10.313 in
Length	48.25 in
Maximum Operating Altitude	12000 ft
Minimum Mounting Spacing on Center (Sea Level) - Phase to	5.4 in (137 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	9.7 in (246 mm)
Thickness - Lug	1.25 in (31.75 mm)
Weight	17 lb
Width	10.313 in

Electrical Ratings

Creep and Leakage Distance	35.4 in (899 mm)
----------------------------	------------------

Duty Cycle	15 kV
Frequency Rating	48-62 Hz
MCOV	12.7 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	43.4 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 31.9 kV @ 1.5 kA• 33.5 kV @ 3 kA• 35.2 kV @ 5 kA• 37.7 kV @ 10 kA• 40.8 kV @ 20 kA• 46.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	29.9 kV
Pressure Relief Capability-Symmetrical rms (kA)	63
Withstand Voltage - 60 Hz Wet Impulse	75 kV
Withstand Voltage - Lightning Impulse	153 kV
Withstand Voltage - Switching Impulse	128 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	IEEE/IEC

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [Installation Manuals - EVP Polymer Station Class Arrester Installation Instructions](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Polymer Station Arrester](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - EVP0013003001 \(for reference only\)](#)
- [Specifications - Specification for Solid Core IEC Station Class Arresters](#)
- [Specifications - EVP0013003001](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)