

Quadri*Sil Braced Line Post Insulator

By OHIO BRASS
Catalog # [BLP055F00000](#)

Quadri*Sil Braced Line Post 161kV, Flat base



*Representative Image

Features

- Combines a suspension and post insulator for increased mechanical capabilities
- Higher transverse capacity
- Increased vertical loading
- Compact design reduces right-of-way

Application

Horizontal V Assembly

General

Fitting - Ground End	Aluminum Flat
Fitting - Live Line End	Two Hole Blade
Material	Silicone
Material - End Fitting	Galvanized Steel
Shed Style	Uniform
Strength Rating - Minimum Ultimate, Longitudinal (L)	1300 lb
Strength Rating - Minimum Ultimate, Vertical (V)	10240 lb
Tensile Strength	7500 lb.
Type	Horizontal V Assembly

Dimensions

Angle	12
Diameter - Shed(s)	5.06
Dimensions	12 in x 10 in x 66.0 in
Distance From Pole	24 in
Height	66.0 in
Length	12 in
Length - Brace Section	78.6
Length - Effective	69.2 in
Length - Suspension Insulator	71.6
Rod Diameter	2.5
Width	10 in

Electrical Ratings

Arc Distance - Dry	54.4
Creep and Leakage Distance	145
Critical Impulse Flashover (CIFO) - Negative	890
Critical Impulse Flashover (CIFO) - Positive	830
Flashover Voltage - 60 Hz Dry	530 kV
Flashover Voltage - 60 Hz Wet	470 kV
Voltage Rating	161 V
Withstand Voltage - 60 Hz Dry	530
Withstand Voltage - 60 Hz Wet	350 kV
Withstand Voltage - Lightning Impulse (Negative)	800 kV
Withstand Voltage - Lightning Impulse (Positive)	745 kV

Certifications and Compliance

Industry Standard(s)	ANSI
----------------------	------

Product Assets

[Catalogs - Quadri*Sil Braced Line Post Insulators Catalog \(CA08051E\)](#)

[Sales Drawings - Quadri Sil Braced Line Post Assy \(BLP055F00000\) \(Reference Only\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)

[Video - Ohio Brass Vertical Load Test-345KV BLP-250 series post-R01 \(VI0820E\)](#)

