

## Quadri\*Sil Braced Line Post Insulator

By OHIO BRASS  
Catalog # [BLP075F12000](#)

Quadri\*Sil Braced Line Post 230kV, Flat base



\*Representative Image

### Features

- Combines a suspension and post insulator for increased mechanical capabilities
- Higher transverse capacity
- Increased vertical loading
- Compact design reduces right-of-way

### Application

Braced Line Post

### General

Fitting - Ground End	Aluminum Flat
Fitting - Live Line End	Two Hole Blade
Material	Silicone
Material - End Fitting	Galvanized Steel
Shed Style	Uniform
Strength Rating - Minimum Ultimate, Longitudinal (L)	985 lb
Strength Rating - Minimum Ultimate, Vertical (V)	11220 lb
Tensile Strength	7500 lb.
Type	Braced Line Post
UPC	096359697275

### Dimensions

Angle	12
Diameter - Shed(s)	5.06
Dimensions	123 in x 10 in x 26.26 in
Distance From Pole	2 in
Height	26.26 in
Length	123 in
Length - Brace Section	128
Length - Effective	86.6 in
Length - Suspension Insulator	121.3
Rod Diameter	2.5
Weight	98.5 lb
Width	10 in

### Electrical Ratings

Arc Distance - Dry	74
Creep and Leakage Distance	196
Critical Impulse Flashover (CIFO) - Negative	1240
Critical Impulse Flashover (CIFO) - Positive	1140
Flashover Voltage - 60 Hz Dry	745kV
Flashover Voltage - 60 Hz Wet	640 kV
Voltage Rating	230 V
Withstand Voltage - 60 Hz Dry	745
Withstand Voltage - 60 Hz Wet	480 kV
Withstand Voltage - Lightning Impulse (Negative)	1115 kV
Withstand Voltage - Lightning Impulse (Positive)	1025 kV

### Certifications and Compliance

Industry Standard(s)	ANSI
----------------------	------

### Product Assets

[Catalogs - Quadri\\*Sil Braced Line Post Insulators Catalog \(CA08051E\)](#)

[Sales Drawings - Quadri Sil Braced Line Post Assy \(BLP075F12000\) \(Reference Only\)](#)

[Test Documents - BLP075X12000](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)

[Video - Ohio Brass Vertical Load Test-345KV BLP-250 series post-R01 \(VI0820E\)](#)

