

EVP Arrester (57 kV MCOV / Uc)

By OHIO BRASS
Catalog # [EVP0057003001](#)

IEEE Station Class / IEC Station Medium Polymer Housed Surge Arrester

Features

- EVP solid core station arresters comply with the latest revision of IEEE C62.11 and IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

General

Cantilever Bending Strength - Max.	20,000 lb.
Catalog Number	EVP0057003001
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Hardware	Single Eyebolt Terminals
Mounting Position	Upright
Type	Station
UPC	096359505297

Dimensions

Diameter - Bolt Circle Variable	8.75 to 10 in
Diameter - Lug Hole	.56 in (14.224 mm)
Diameter - Single Bolt Hole(s)	0.5 in
Dimensions	42.000 in x 15.500 in x 20.000 in
Height	20 in
Length	42 in
Maximum Operating Altitude	12000 ft
Minimum Mounting Spacing on Center (Sea Level) - Phase to	19.2 in (488 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	25.4 in (645 mm)
Thickness - Lug	1.25 in (31.75 mm)
Weight	41 lb
Width	15.5 in

Electrical Ratings



Creep and Leakage Distance	82.4 in (2093 mm)
Duty Cycle	72 kV
Frequency Rating	48-62 Hz
MCOV	57 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	192 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 146.6 kV @ 1.5 kA• 154 kV @ 3 kA• 161.5 kV @ 5 kA• 173.2 kV @ 10 kA• 187.3 kV @ 20 kA• 213.6 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	137.4 kV
Pressure Relief Capability- Symmetrical rms (kA)	63
Withstand Voltage - 60 Hz Wet Impulse	194 kV
Withstand Voltage - Lightning Impulse	421 kV
Withstand Voltage - Switching Impulse	353 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	IEEE/IEC

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [Installation Manuals - EVP Polymer Station Class Arrester](#)
- [Installation Instructions](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Polymer Station Arrester](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - EVP0057003001 \(for reference only\)](#)
- [Specifications - EVP0057003001](#)
- [Specifications - Specification for Solid Core IEC Station Class Arresters](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
OB-EVP0057003001-SPEC-EN | REV 3/2025