

HUBBELL Power Systems

MVN Arrester (131 kV MCOV)

By OHIO BRASS

Catalog # [MVN168GA131AA](#)

IEEE Station Class Porcelain Housed Surge Arrester



Features

- IEEE porcelain station class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Cantilever Bending Strength - Max.	150,000 in lbs
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	Porcelain Housing
Mounting Hardware	Single Eyebolt Terminals
Mounting Position	Metal Top/Tripod Base
Type	Station
UPC	096359506546

Dimensions

Bolt Circle Diameter	10 in
Diameter - Lug Hole	.88 in (22.352 mm)
Diameter - Single Bolt Hole(s)	0.75 in
Height	76.6 in
Maximum Operating Altitude	12000 ft
Minimum Mounting Spacing on Center (Sea Level) - Phase to	36 in (914 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to	46 in (1168 mm)
Phase	
Thickness - Lug	1.25 in (31.75 mm)

Electrical Ratings

Creep and Leakage Distance	175 in (4445 mm)
Duty Cycle	168 kV
Frequency Rating	48-62 Hz
MCOV	131 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	412 kV
Maximum Discharge Voltage	337 kV @ 1.5 kA
	350 kV @ 3 kA
	362 kV @ 5 kA
	380 kV @ 10 kA
	406 kV @ 20 kA
	447 kV @ 40 kA
Maximum Switching Surge Protective Level @ 1000A	322
Pressure Relief Capability-Symmetrical rms (kA)	65

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-MVNI68GA131AA-SPEC-EN | REV 6/2024