

HUBBELL Power Systems

MVN Arrester (140 kV MCOV)

By OHIO BRASS

Catalog # [MVN172GA140AA](#)

IEEE Station Class Porcelain Housed Surge Arrester



Features

- IEEE porcelain station class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Cantilever Bending Strength - Max.	150,000 in lbs
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	Porcelain Housing
Mounting Hardware	Single Eyebolt Terminals
Mounting Position	Metal Top/Tripod Base
Type	Station
UPC	096359506553

Dimensions

Bolt Circle Diameter	10 in
Diameter - Lug Hole	.88 in (22.352 mm)
Diameter - Ring	25.2 in / 15.0 in
Diameter - Single Bolt Hole(s)	0.75 in
Height	82.6 in
Maximum Operating Altitude	12000 ft
Minimum Mounting Spacing on Center (Sea Level) - Phase to	44 in (1118 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to	51 in (1295 mm)
Phase	
Thickness - Lug	1.25 in (31.75 mm)

Electrical Ratings

Creep and Leakage Distance	175 in (4445 mm)
Duty Cycle	172 kV
Frequency Rating	48-62 Hz
MCOV	140 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	441 kV
Maximum Discharge Voltage	360 kV @ 1.5 kA
	374 kV @ 3 kA
	387 kV @ 5 kA
	406 kV @ 10 kA
	434 kV @ 20 kA
	477 kV @ 40 kA
Maximum Switching Surge Protective Level @ 1000A	344
Pressure Relief Capability-Symmetrical rms (kA)	65

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-MVN172GA140AA-SPEC-EN | REV 6/2024