

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250024S9020](#)



2.5" Line Post, Standard Leak, Long Two Hole Blade,
Aluminum Gain Base with 12" CL holes for 7/8" bolts

*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	5420 LB
Cantilever Bending Strength - Routine	2710 LB
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Aluminum Gain
Fitting - Live Line End	Long Tear Drop Blade
Number of Sheds	20
Shed Style	Uniform
Tensile Strength	15000 lb.
UPC	096359484271

Dimensions

Diameter - Shed(s)	5.06
Length - Effective	36.9 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM
Width	8.06 in

Electrical Ratings

Arc Distance - Dry	25 IN (635 MM)
Creep and Leakage Distance	63 IN (1600 MM)
Critical Impulse Flashover (CIFO) - Negative	505
Critical Impulse Flashover (CIFO) - Positive	385
Flashover Voltage - 60 Hz Dry	255
Flashover Voltage - 60 Hz Wet	235
kV Class	69.00 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod \(R18-01-03\)](#)
[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)
[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)
[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)