

HUBBELL

Power Systems

Quadri*Sil Vertical Line Post Insulator

By OHIO BRASS
Catalog # [P250026S2050](#)

2.5" Line Post, Standard Leak, Vertical Clamptop, 5" Bolt Circle with 5/8" Thru Holes



Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	4890 LB
Cantilever Bending Strength - Routine	2445 LB
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	5" Bolt Circle, 5/8" tapped hole
Fitting - Live Line End	Vertical Clamptop
Number of Sheds	22
Shed Style	Uniform
UPC	096359511229

Dimensions

Diameter - Shed(s)	5.06
Length - Effective	37.5 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	27.4 IN (695 MM)
Creep and Leakage Distance	70 IN (1778 MM)
Critical Impulse Flashover (CIFO) - Negative	540
Critical Impulse Flashover (CIFO) - Positive	425
Flashover Voltage - 60 Hz Dry	280
Flashover Voltage - 60 Hz Wet	255
kV Class	69 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod](#)



A Hubbell brand