

EVP Arrester (17 kV MCOV / Uc)

By OHIO BRASS

Catalog # [EVP3017003003](#)

IEEE Station Class / IEC Station Medium Polymer Housed Surge Arrester



Features

- EVP solid core station arresters comply with the latest revision of IEEE C62.11 and IEC 60099-4
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Robust sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Assembled in Aiken, South Carolina
- 100% routine tested

General

Catalog Number	EVP3017003003
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Station

Electrical Ratings

Creep and Leakage Distance	40.5 in (1029 mm)
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond Discharge Volts @ Classifying	57.8

Current

Maximum Discharge Voltage	<ul style="list-style-type: none">• 42.7 kV @ 1.5 kA• 44.9 kV @ 3 kA• 47.1 kV @ 5 kA• 50.5 kV @ 10 kA• 54.6 kV @ 20 kA• 62.3 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	40.1
Pressure Relief Capability-Symmetrical rms (kA)	63

Certifications And Compliance

Industry Standard(s)	IEEE/IEC
----------------------	----------

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Polymer Station Arrester](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - EVP3017003003 \(for reference only\)](#)
- [Specifications - EVP3017003003](#)
- [Specifications - Specification for Solid Core IEC Station Class Arresters](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)