

Mity*Lite Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250017H0500](#)



High strength 69 kV post, 2 hole blade, Rigid gain base

Features

- Compact design to provide the same electrical characteristics with increased mechanical strength compared to our current 69 kV Veri*Lite Line Posts
- Patented Quadri*Sil four point sealing system to protect the critical triple point.

General

Cantilever Bending Strength - Max.	6180 lb
Cantilever Bending Strength - Routine	3090 lb
Catalog Number	P250017H0500
Fitting - Ground/Base	Rigid Gain Base
Fitting - Live Line End	Tear Drop Blade
Material	Silicone Rubber
Number of Sheds	10
UPC	096359718031

Dimensions

Diameter - Large Shed	10.08 in
Diameter - Small Shed	6.96 in
Dimensions	30.5 in x 6.96 in x 15.60 in

Height	15.6 in
Length	30.5 in
Length - Effective	29.4 in
Rod Diameter	2.5 in
Weight	50 lb
Width	6.96 in

Electrical Ratings

Arc Distance - Dry	23.1 in (587 mm)
Creep and Leakage Distance	60 in (1524mm)
Critical Impulse Flashover (CIFO) - Negative	470 kV
Critical Impulse Flashover (CIFO) - Positive	360 kV
Flashover Voltage - 60 Hz Dry	230 kV
Flashover Voltage - 60 Hz Wet	180 kV
Voltage Rating	69 kV

Product Assets

[Catalogs - Veri*Lite Line Post Insulators Catalog](#)
[Literature - Silicone Insulators](#)
[Sales Drawings - Quadri*Sil line post series 250](#)
[Specifications - P250017H0500](#)