


Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250021S0080](#)



2.5" Line Post, Standard Leak, Two Hole Blade, Steel Flat Base with 12" CL and 8"x13" holes for 7/8" bolts

*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	5910 LB
Cantilever Bending Strength - Routine	2955 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	18
Shed Style	Uniform

Dimensions

Angle	12
Diameter - Shed(s)	5.06
Length	15 in
Length - Effective	34.6 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM
Width	8.06 in

Electrical Ratings

Arc Distance - Dry	22.5 IN (571 MM)
Creep and Leakage Distance	57 IN (1448 MM)
Critical Impulse Flashover (CIFO) - Negative	455
Critical Impulse Flashover (CIFO) - Positive	340
Flashover Voltage - 60 Hz Dry	220
Flashover Voltage - 60 Hz Wet	200
kV Class	69.00 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod \(R18-01-03\)](#)
[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)
[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)
[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)