


## Quadri\*Sil Vertical Line Post Insulator

By OHIO BRASS  
Catalog # P250026S3150

2.5" Line Post, Standard Leak, 5" Bolt Circle, 5" Bolt Circle with 5/8" Thru Holes



\*Representative Image

### Features

- Made from hydrophobic silicone polymer

### General

Cantilever Bending Strength - Max.	5000 LB
Cantilever Bending Strength - Routine	2500 LB
Fitting - Ground End	5" Bolt Circle, 5/8" through hole
Fitting - Live Line End	5" (127mm) Bolt Circle 5/8" (16mm) Tapped Hole
Number of Sheds	22
Shed Style	Uniform

### Dimensions

Diameter - Shed(s)	5.06
Length - Effective	36.3 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM

### Electrical Ratings

Arc Distance - Dry	27.4 IN (695 MM)
Creep and Leakage Distance	69 IN (1753 MM)
Critical Impulse Flashover (CIFO) - Negative	540
Critical Impulse Flashover (CIFO) - Positive	425
Flashover Voltage - 60 Hz Dry	280
Flashover Voltage - 60 Hz Wet	255
kV Class	69.00 kV

### Product Assets

[Catalogs - Quadri\\*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)  
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri\\*Sil Line Post Insulators - 2.5" Rod \(R18-01-03\)](#)  
[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)  
[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)  
[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)