

HUBBELL

Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250036S1070](#)

2.5" Line Post, Standard Leak, Horizontal Clamptop, Steel Gain
Base with 12" CL holes for 7/8" bolts



Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	3760 LB
Cantilever Bending Strength - Routine	1880 LB
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Horizontal Clamptop
Number of Sheds	30
Shed Style	Uniform
UPC	096359442059

Dimensions

Angle	12
Diameter - Shed(s)	5.06
Length	15 in
Length - Effective	49.5 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM
Width	8.35 in

Electrical Ratings

Arc Distance - Dry	37.1 IN (942 MM)
Creep and Leakage Distance	95 IN (2413 MM)
Critical Impulse Flashover (CIFO) - Negative	690
Critical Impulse Flashover (CIFO) - Positive	580
Flashover Voltage - 60 Hz Dry	380
Flashover Voltage - 60 Hz Wet	345
kV Class	138 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod](#)



A Hubbell brand