

HUBBELL

Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250055S9080](#)

2.5" Line Post, Standard Leak, Long Two Hole Blade, Steel Flat Base with 12" CL and 8"x13" holes for 7/8" bolts



Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	2600 LB
Cantilever Bending Strength - Routine	1300 lb (5.8 kN)
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Long Tear Drop Blade
Number of Sheds	46
Shed Style	Uniform

Dimensions

Diameter - Shed(s)	5.06
Length	15 in
Length - Effective	67.7 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM
Width	8.06 in

Electrical Ratings

Arc Distance - Dry	56.4 IN (1432 MM)
Creep and Leakage Distance	145 IN (3683 MM)
Critical Impulse Flashover (CIFO) - Negative	990
Critical Impulse Flashover (CIFO) - Positive	885
Flashover Voltage - 60 Hz Dry	580
Flashover Voltage - 60 Hz Wet	510
kV Class	161 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod](#)



A Hubbell brand