

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250065S1020](#)



2.5" Line Post, Standard Leak, Horizontal Clamptop, Aluminum Gain Base with 12" CL holes for 7/8" bolts

*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	2220 LB
Cantilever Bending Strength - Routine	1110 LB
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Aluminum Gain
Fitting - Live Line End	Horizontal Clamptop
Number of Sheds	54
Shed Style	Uniform
UPC	096359522799

Dimensions

Angle	12
Diameter - Shed(s)	5.06
Length	14 in
Length - Effective	77.9 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM
Width	8.06 in

Electrical Ratings

Arc Distance - Dry	66.1 IN (1678 MM)
Creep and Leakage Distance	170 IN (4318 MM)
Critical Impulse Flashover (CIFO) - Negative	1140
Critical Impulse Flashover (CIFO) - Positive	1035
Flashover Voltage - 60 Hz Dry	675
Flashover Voltage - 60 Hz Wet	580
kV Class	230.00 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod \(R18-01-03\)](#)
[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)
[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)
[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)