


Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # P250118S008B

2.5" Line Post, Standard Leak, Long Two Hole Blade, Steel Flat Base with 12" CL and 8"x13" holes for 7/8" bolts, with 15" Corona Ring



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	1270 LB
Cantilever Bending Strength - Routine	635 LB
Fitting - Ground End	Steel Flat
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	98
Shed Style	Uniform
UPC	096359697909

Dimensions

Diameter - Shed(s)	5.06
Length - Effective	129.2 in
Rod Diameter	2.500 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	119.3 IN (3030 MM)
Creep and Leakage Distance	309 IN (7849 MM)
Critical Impulse Flashover (CIFO) - Negative	1940
Critical Impulse Flashover (CIFO) - Positive	1855
Flashover Voltage - 60 Hz Dry	1150
Flashover Voltage - 60 Hz Wet	920
kV Class	345.00 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod \(R18-01-03\)](#)
[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)
[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)
[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)