

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250118S107B](#)



2.5" Line Post, Standard Leak, Horizontal Clamptop, Steel Gain Base with 12" CL holes for 7/8" bolts, with 15" Corona Ring

Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	1270 LB
Cantilever Bending Strength - Routine	635 LB
Catalog Number	P250118S107B
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Horizontal Clamptop
Number of Sheds	98
Shed Style	Uniform

Dimensions

Diameter - Shed(s)	5.06
Length - Effective	130 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	119.3 IN (3030 MM)
Creep and Leakage Distance	309 IN (7849 MM)
Critical Impulse Flashover (CIFO) - Negative	1940
Critical Impulse Flashover (CIFO) - Positive	1855
Flashover Voltage - 60 Hz Dry	1150
Flashover Voltage - 60 Hz Wet	920
kV Class	345 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Literature - Silicone Insulators](#)
[Specifications - P250118S107B](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators – 2.5" Rod](#)
[Video - Ohio Brass Polymer Insulator Tester](#)
[Video - Ohio Brass Insulator Crate Packaging](#)
[Video - Ohio Brass Vertical Load Test-345KV BLP-250 series post-R01](#)