

Quadri*Sil Horizontal Line Post
Insulator

By OHIO BRASS
Catalog # [P300078S1030](#)



3" Line Post, Standard Leak, Horizontal Clamptop, Aluminum
Gain Base with 9"x13" holes for 7/8" bolts

*Representative Image

Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	3240 LB
Cantilever Bending Strength - Routine	1620 LB
Catalog Number	P300078S1030
Fitting - Ground End	Aluminum Flat
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	65
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	15 in
Length - Effective	91.2 in
Rod Diameter	3 in

Width

10 in

Electrical Ratings

Arc Distance - Dry	81.2 (2062MM)
Creep and Leakage Distance	246 (6246MM)
Critical Impulse Flashover (CIFO) - Negative	1350
Critical Impulse Flashover (CIFO) - Positive	1255
Flashover Voltage - 60 Hz Dry	800
Flashover Voltage - 60 Hz Wet	730
Voltage Rating	230 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Literature - Silicone Insulators](#)
[Specifications - P300078S1030](#)
[Video - Ohio Brass Polymer Insulator Tester](#)
[Video - Ohio Brass Insulator Crate Packaging](#)
[Video - Ohio Brass Vertical Load Test-345KV BLP-250 series post-R01](#)