

PH3 Arrester (66 kV Rated, 2880 mm Creep Distance, AA Hardware)

By OHIO BRASS
Catalog # [PH3072GV066AA](#)

IEC Station Medium / Polymer Housed Surge Arrester

Features

- IEC silicone Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

| | |
|----------------|--------------------------|
| Catalog Number | PH3072GV066AA |
| Color | Gray Housing |
| Material | Silicone Polymer Housing |
| Type | Station |
| UPC | 096359721857 |

Electrical Ratings

| | |
|------------------|----------|
| Frequency Rating | 48-62 Hz |
|------------------|----------|



Pressure Relief Capability- 63
Symmetrical rms (kA)

Certifications And Compliance

Industry Standard(s) IEC

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [Installation Manuals - Polymer Hollow Core Station Class Arrester](#)
- [Installation Instructions](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Specifications - PH3072GV066AA](#)
- [Specifications - Specification for Hollow Core IEC Station Class Arresters](#)
- [Test Documents - IEC Confirmation of Design Testing PH3](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)