

**PH3 Arrester (132 kV Rated, 4370 mm Creep Distance, AA Hardware)**

By OHIO BRASS  
Catalog # [PH3123GH132AA](#)

IEC Station Medium / Polymer Housed Surge Arrester

**Features**

- IEC silicone Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

**General**

Catalog Number	PH3123GH132AA
Color	Gray Housing
Material	Silicone Polymer Housing
Type	Station

**Electrical Ratings**

Frequency Rating	48-62 Hz
Pressure Relief Capability-	63
Symmetrical rms (kA)	



**Certifications And Compliance**

Industry Standard(s) IEC

**Product Assets**

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)  
[Installation Manuals - Polymer Hollow Core Station Class Arrester](#)  
[Installation Instructions](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)  
[Specifications - Specification for Hollow Core IEC Station Class Arresters](#)  
[Specifications - PH3123GH132AA](#)  
[Test Documents - IEC Confirmation of Design Testing PH3](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor](#)