


Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # P250106S103B

2.5" Line Post, Standard Leak, Horizontal Clamptop, Aluminum Flat Base with 12" CL, 8"x10", and 8"x13" holes for 7/8" bolts, with 15" Corona Ring



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	1400 LB
Cantilever Bending Strength - Routine	700 LB
Fitting - Ground End	Aluminum Flat
Fitting - Live Line End	Horizontal Clamptop
Number of Sheds	88
Shed Style	Uniform

Dimensions

Diameter - Shed(s)	5.06
Length - Effective	118.2 in
Rod Diameter	2.500 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	107.2 IN (2722 MM)
Creep and Leakage Distance	278 IN (7061 MM)
Critical Impulse Flashover (CIFO) - Negative	1750
Critical Impulse Flashover (CIFO) - Positive	1665
Flashover Voltage - 60 Hz Dry	1040
Flashover Voltage - 60 Hz Wet	850
kV Class	345.00 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod \(R18-01-03\)](#)
[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)
[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)
[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)