

PH3 Arrester (276 kV Rated, 11610 mm Creep Distance, AA Hardware)

By OHIO BRASS
Catalog # [PH3362GV276AA](#)

IEC Station Medium / Polymer Housed Surge Arrester

Features

- IEC silicone Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Catalog Number	PH3362GV276AA
Color	Gray Housing
Material	Silicone Polymer Housing
Type	Station

Electrical Ratings

Frequency Rating	48-62 Hz
Pressure Relief Capability-	63
Symmetrical rms (kA)	



Certifications And Compliance

Industry Standard(s) IEC

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)
[Installation Manuals - Polymer Hollow Core Station Class Arrester](#)
[Installation Instructions](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Specifications - PH3362GV276AA](#)
[Specifications - Specification for Hollow Core IEC Station Class Arresters](#)
[Test Documents - IEC Confirmation of Design Testing PH3](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)