

## Glass Bell Suspension w/ Zinc Sleeve, 25000 lb

By OHIO BRASS  
Catalog # [PSN12146DC](#)



5-3/4" x 10" Glass Bell Suspension w/ Zinc Sleeve.

### Features

- Dielectric made of toughened glass, hot-dip galvanized ductile iron cap and forged steel pin, stainless steel split pin for coupling of units
- Easy inspection and mechanical reliability
- High thermal and mechanical resistance
- Reduced aging
- High dielectric resistance and homogenous potential distribution

### Application

Glass Bell Suspension

### General

Break Strength	45 N-m (400 lb-in)
Catalog Number	PSN12146DC
Fitting - Ground/Base	52-5-L Socket
Fitting - Live Line End	52-5-L Ball
Material	Glass
Material - End Fitting	Galvanized Steel w/ Zinc Sleeve
Strength Rating - Ultimate	25000 lb
UPC	096359678793

### Dimensions

Diameter - Bell	10" (255 mm)
Height	5.75 in
Weight	8.6 lb

### Electrical Ratings

Creep and Leakage Distance	12.62 (320 mm)
Critical Impulse Flashover (CIFO) - Negative	130 kV
Critical Impulse Flashover (CIFO) - Positive	125 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

### Certifications And Compliance

Industry Standard(s)	ANSI C.29.2.B
----------------------	---------------

### Logistics

Pallet Quantity	90
Standard Package	6

### Product Assets

[Catalogs - Toughened Glass Insulators Catalog](#)  
[Literature - Silicone Insulators](#)  
[Sales Drawings - Glass Insulator 52-5 L \(Reference Only\)](#)  
[Specifications - PSN12146DC](#)  
[Video - Ohio Brass SGD Glass Insulator](#)