

HUBBELL

Power Systems

Glass Bell Suspension, 15000 lb

By OHIO BRASS
Catalog # [PSN70146](#)

5-3/4" x 10" Glass Bell Suspension.



Features

- Dielectric made of toughened glass, hot-dip galvanized ductile iron cap and forged steel pin, stainless steel split pin for coupling of units
- Easy inspection and mechanical reliability
- High thermal and mechanical resistance
- Reduced aging
- High dielectric resistance and homogenous potential distribution

General

Application	Glass Bell Suspension
Break Strength	45 N·m (400 lb-in)
Fitting - Ground/Base	52-3-L Socket
Fitting - Live Line End	52-3-L Ball
Material	Glass
Material - End Fitting	Galvanized Steel
Strength Rating - Ultimate	15000 lb
UPC	096359678823

Dimensions

Diameter - Bell	10" (255 mm)
Height	5.75 in
Weight	7.7 lb

Electrical Ratings

Creep and Leakage Distance	12.5" (318 mm)
Critical Impulse Flashover (CIFO) - Negative	130 kV
Critical Impulse Flashover (CIFO) - Positive	125 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

Certifications And Compliance

Industry Standard(s)	ANSI C.29.2.B
----------------------	---------------

Logistics

Pallet Quantity	90
Standard Package	6

Product Assets

[Catalogs - Toughened Glass Insulators Catalog](#)
[Sales Drawings - Glass Insulator 52-3L \(Reference Only\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-PSN70146-SPEC-EN | REV 6/2024