

HUBBELL

Power Systems

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250118S0020](#)

2.5" Line Post, Standard Leak, Two Hole Blade, Aluminum Gain
Base with 12" CL holes for 7/8" bolts



Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	1270 LB
Cantilever Bending Strength - Routine	635 LB
Fitting - Ground End	Aluminum Gain
Fitting - Live Line End	Tear Drop Blade
Number of Sheds	98
Shed Style	Uniform

Dimensions

Angle	12
Diameter - Shed(s)	5.06
Length	14 in
Length - Effective	129.2 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM
Width	8.06 in

Electrical Ratings

Arc Distance - Dry	119.3 IN (3030 MM)
Creep and Leakage Distance	309 IN (7849 MM)
Critical Impulse Flashover (CIFO) - Negative	1960
Critical Impulse Flashover (CIFO) - Positive	1875
Flashover Voltage - 60 Hz Dry	1170
Flashover Voltage - 60 Hz Wet	930
kV Class	345 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)

[Sales Drawings - Quadri*Sil Line Post Series 250 \(Reference Only\)](#)

[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators - 2.5" Rod](#)



A Hubbell brand