

HUBBELL Power Systems

Quadri*Sil Suspension Insulator

By OHIO BRASS

Catalog # [S025040S0000](#)

25kip Standard leak, Eye Eye



*Representative Image

Features

Made from hydrophobic silicone polymer

General

EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Chain Eye
Fitting - Live Line End	Chain Eye
Material	Silicone Rubber
Material - End Fitting	Ductile Iron
Number of Sheds	38
Shed Style	Uniform
Strength Rating - Ultimate	25000 lb
Tensile Strength	25 kip, 5/8" (16 mm)
Tensile Strength - Routine	12,500 lbs
UPC	096359510789

Dimensions

Diameter - Shed(s)	2.9 IN
Length - Effective	54.38 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	41 IN (1040 MM)
Creep and Leakage Distance	105 IN (2654 MM)
Critical Impulse Flashover (CIFO) - Negative	590 kV
Critical Impulse Flashover (CIFO) - Positive	600 kV
Flashover Voltage - 60 Hz Dry	435 kV
Flashover Voltage - 60 Hz Wet	415 kV
Withstand Voltage - 60 Hz Wet	255 kV
Withstand Voltage - Lightning Impulse (Negative)	685 kV
Withstand Voltage - Lightning Impulse (Positive)	695 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Test Documents - Prototype Test Report - Quadri*Sil Suspension Insulators - 5/8" Rod](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-S025040S0000-SPEC-EN | REV 6/2024