

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P250126S9070](#)



2.5" Line Post, Standard Leak, Long Two Hole Blade, Steel Gain
Base with 12" CL holes for 7/8" bolts

Features

Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	1200 LB
Cantilever Bending Strength - Routine	600 LB
Catalog Number	P250126S9070
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Long Tear Drop Blade
Number of Sheds	104
Shed Style	Uniform

Dimensions

Diameter - Shed(s)	5.06
Length	12 in
Length - Effective	136.4 in
Rod Diameter	2.5 in
Thickness - Housing	> 3MM
Width	8.06 in

Electrical Ratings

Arc Distance - Dry	126.6 IN (3215 MM)
Creep and Leakage Distance	328 IN (8331 MM)
Critical Impulse Flashover (CIFO) - Negative	2050
Critical Impulse Flashover (CIFO) - Positive	1975
Flashover Voltage - 60 Hz Dry	1215
Flashover Voltage - 60 Hz Wet	960
kV Class	500 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Literature - Silicone Insulators](#)
[Specifications - P250126S9070](#)
[Test Documents - ANSI C29.17 Prototype Test Report; Quadri*Sil Line Post Insulators – 2.5" Rod](#)
[Video - Ohio Brass Polymer Insulator Tester](#)
[Video - Ohio Brass Insulator Crate Packaging](#)
[Video - Ohio Brass Vertical Load Test-345KV BLP-250 series post-R01](#)