

Quadri*Sil Horizontal Line Post Insulator

By OHIO BRASS
Catalog # [P300085S1030](#)



3" Line Post, Standard Leak, Horizontal Clamptop, Aluminum Gain Base with 9"x13" holes for 7/8" bolts

*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Cantilever Bending Strength - Max.	3020 LB
Cantilever Bending Strength - Routine	1510 LB
Fitting - Ground End	Aluminum Flat
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	70
Shed Style	Uniform

Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	15 in
Length - Effective	97.1 in
Rod Diameter	3.000 in
Width	10 in

Electrical Ratings

Arc Distance - Dry	87.4 (2220MM)
Creep and Leakage Distance	265 (6721MM)
Critical Impulse Flashover (CIFO) - Negative	1445
Critical Impulse Flashover (CIFO) - Positive	1370
Flashover Voltage - 60 Hz Dry	860
Flashover Voltage - 60 Hz Wet	790
Voltage Rating	230 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)